

ALUMINIUM SLIDING TRACK

04/11/2021

APPLICATION

The Slider's precision made components and exclusive features make it the ideal sliding system for Display Cabinets, Cocktail Cabinets, Cupboards, and Interior Reception Windows. Single, double or triple slides can be arranged to suit the various requirements.

DOUBLE GLAZING

The track is suitable for double glazing twin window system.

COLOUR

Anodised silver.

STANDARD SET

List of Components:

- Top Guide

Top Guide is pre-drilled and countersunk for easy fixing.

- Glass Rails
- End Caps
- Rollers

Glass Rail with clip on End Caps and quiet, easy action Nylon Rollers.

Bottom Track

Bottom Track double or single to suit. Pre-drilled.

- Mohair Strips
- Screws
- Glazing Gaskets

LOCKING

Sliding Track Lock is interchangable from left to right hand. Available in satin finish only. Not suitable as a handle in high use situations, Glasscorp recommends a Finger Pull or Plunger Lock. Plunger Lock can be used in the centre glass as a handle.


PRODUC	T INFORMATION	
RS1200	Track Set	1200mm, 2 panels
RS1500	Track Set	1500mm, 2 panels
RS1800	Track Set	1800mm, 2 panels
	Track Sets also available in	full 3600mm lengths
6716SA	Track - Glass Rail	1m
6716S	Track - Glass Rail	3.6m
6354SA	Track - Single Top	1m
6354S	Track - Single Top	3.6m
6355SA	Track - Single Bottom	1m
6355S	Track - Single Bottom	3.6m
6352SA	Track - Double Top	1m
6352S	Track - Double Top	3.6m
6353SA	Track - Double Bottom	1m
6353S	Track - Double Bottom	3.6m
EC	End Cap	1
NR	Nylon Rollers	1
LLH	Sliding Track Lock	Left/Right Hand
MH	Mohair for Sliding Track	1m
LPL	Plunger Lock	1
FP1A	Finger Pulls Chrome - Closed	1
FP1	Finger Pulls Chrome - Closed	100 Pack
GGA	Sliding Track Glazing Gasket - 6mm	1m
NRSA	Sliding Track Screw	1
NRP	Sliding Track Roller Pack	x4 EC x4 NR x20 NRSA


ALUMINIUM SLIDING TRACK DS Page 1 of 2

GLASS / VENEER SIZES

Height = Opening height minus 30mm Width = Half opening width plus 18mm

This gives a 36mm lap at centre





SECTION SCALE 1:1

ALUMINIUM SLIDING TRACK DS Page 2 of 2